

**PRODUCT**

# ESD Sole Grounder

**FEATURES**

- Hook and loop type with D Ring for size adjustment
- Double layers, conductive cup
- 3/4" Black hook and loop
- 2 pcs D-Ring
- 3/4" Elastic Strap

Open the buckle and hook and loop straps. Place the sole grounder on the bottom of the shoe. Close the toe strap by feeding the velcro through the plastic ring. Close the ankle strap. Place the ribbon inside the sock or shoe.


**SPECIFICATIONS**

DETAILS	TYPICAL VALUE
Outer conductive surface (black)	10 <sup>3</sup> - 10 <sup>5</sup> Ohms
Inner antistatic surface (ivory)	10 <sup>7</sup> - 10 <sup>8</sup> Ohms
Conductive tab	10 <sup>3</sup> - 10 <sup>4</sup> Ohms
Resistance	1Meg Resistor Built in

PRODUCT CODE	DESCRIPTION	SIZE (mm)	NOTES
068-0020	ESD Sole Grounder	Small (160 x 168)	Each
068-0021	ESD Sole Grounder	Medium (165 x 185)	Each
068-0022	ESD Sole Grounder	Large (170 x 210)	Each
068-0023	ESD Sole Grounder	X Large (175 x 228)	Each

To request a quotation or for more information, please call **+44 (0)1473 836200**  
 email [info@antistat.co.uk](mailto:info@antistat.co.uk) or visit [www.antistat.co.uk](http://www.antistat.co.uk)