



- A. Constructed of a lightweight dissipative material which is made from texturized polyester and a minimum of 9% carbon nylon monofiliment*

 Can be washed multiple times in a mild detergent**.
- B. A nose wire helps ensure mask fits securely
- C. Elastic bands range from Small-Medium (2.75") to Large-Extra Large (3.25"). The mask area is the same size for all items. (D x E)

Specifications

Fabric Weight* 2.2 oz per square yard

Fabric Content Texturized polyester and a minimum of 9% carbon mono-filament nylon. Carbon Mono-filament Conductive at 1 x 10^4 ohms, nonflaking and non-sloughing. Surface Resistance 1 x 10^5 < 1 x 10^7 ohms, per ANSI/ESD STM2.1 and ESD TR53 of Fabrics

Glass Transition Temp 250°F

Flash Point 1040°F

*Fabric lots vary slightly in color and weight.

Mask Selection		
Item #	Color	Strap Size
97550	Blue	Small-Medium
<u>97551</u>	White	Small-Medium
97552	Gray	Small-Medium
<u>97553</u>	Blue	Large-Extra Large
<u>97554</u>	White	Large-Extra Large
<u>97555</u>	Gray	Large-Extra Large



Unless otherwise noted, tolerance ± 1/2"

**Mask Laundering

The mask should be laundered periodically. Woolite works well. Liquid detergents are better than dry in that there is less caking and frictional wear. Launder mask in cool or warm water, tumble dry with low heat or hang dry. Machine washing works well if using a standard house machine on gentle cycle. It is not recommended to launder these masks in heavy industrial laundry machines as it will lead to premature wear. Masks should be tumbled dry using low heat. DO NOT BLEACH. After laundering, verify (Rgp) < 1 x 10^7 ohms.

STATIC DISSIPATIVE FACEMASKS

DESCO WEST: 3651 WALNUT AVE, CHINO, CA 91710 WEBSITE: <u>Desco.com</u> PHONE: (909) 627-8178

DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407

PHONE: (781) 821-8370

DRAWING NUMBER 97550 DATE: December 2020

DESCO